

# NOVATECH

FTP200X75-Ø25 HL75

EAN 4031582428827



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	75 mm
Axle hole diameter	25 mm
Hub length	75 mm
Hardness of tread (A)	92 Shore A

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	7.988 kg

## TECHNICAL DRAWINGS

