PRODUCT INFORMATION

ALPHA

3478UOR200P63

EAN 4031582307115



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Alpha
CO2 emission (scope 3)	9.95
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	350 kg
Electric Conductive	No
Stainless	No
WeAssist Compatible	
Load capacity Static	700 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall Height	240 mm
Overall width	115 mm
Overall weight	2 kg

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Broad
Housing Color	Blue passivated

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Roller bearing
Axle	Screwed with nut
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Medium rectangular plate
Plate length	140 mm
Plate width	115 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

© Copyright 2026 TENTE International GmbH


ALPHA


3478UOR200P63

EAN 4031582307115

Order number 00003029

Product Drawings





© Copyright 2026 TENTE International GmbH