

AGILA

2478DYK125P50

EAN 4031582340549



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Agila
Type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	Yes
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall Height	160 mm
Overall width	60 mm
Overall weight	1 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Housing Color	Blue passivated
Dome diameter	60 mm

WHEEL

Body material	Sheet Steel
Tread Material Mix	Solid rubber, black, electric-conductive
Bearing	Cone ball bearing
Wheel Color	Blue passivated
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	80 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	77 mm
Plate width	67 mm
Plate hole length (Minimum)	46.5 mm
Plate hole length (Maximum)	51.5 mm
Plate hole width (Minimum)	56 mm
Plate hole width (Maximum)	61.5 mm
Plate hole diameter	8.5 mm

AGILA

2478DYK125P50

EAN 4031582340549

Order number 00006676

Product Drawings



BETTER MOBILITY. BETTER LIFE.

