

# ALPHA

3477PJP100P30-13

EAN 4031582409703



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	110 kg
Load capacity Static	220 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	128 mm
Overall weight	1006 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	100 mm
Tread width	35 mm
Hardness of tread (A)	85 Shore A

## HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	41 mm
Swivel radius	123 mm
Swivel interference	246 mm

## FITTING

Fitting type	Bolt hole
--------------	-----------

# ALPHA

3477PJP100P30-13

EAN 4031582409703



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

