

PRODUCT INFORMATION

ELASTECH HEAT

IDG 100x35 yellow HL45,5 asm.

EAN 4031582347203



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Aluminium
Tread Material Mix	Damping, heat resistant
Bearing	Dry bearing bush
Wheel Color	Metallic
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Axle Hole Diameter	8 mm
Hub Length	45.5 mm
Body width	35 mm
Hardness of tread (A)	75 Shore A

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●●○
Attrition	●●○○○
Corrosion Resistance	●●●●●

CORE ATTRIBUTES

Product Name	Elastech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	80 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	160 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	250 °C
Overall weight	0.54 kg

ELASTECH HEAT

IDG 100x35 yellow HL45,5 asm.

EAN 4031582347203

Order number 00033962
Product Drawings



BETTER MOBILITY. BETTER LIFE.

