

INTEGRAL ASSIST

ED44ETW150R36-34S35 D 9002 270°

Order number 990067061



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll Performance | ● ● ● ● ● |
| Movement Noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|---------------------------------|---|
| Product Name | Integral assist |
| Type | Swivel castor with central, total or directional lock |
| Standard | EN12531 - Hospital Bed Castors |
| Load capacity at 4 km/h | 150 kg |
| Electric Conductive | No |
| Stainless | No |
| WeAssist Compatible | 1 |
| Load capacity Static | 450 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall Height | 183 mm |
| Overall width | 110.5 mm |
| Overall weight | 4.68 kg |
| Protection type | IPX6 (only for electronic components when installed) |
| Permissible ambient temperature | Operating temperature 5 °C to 40 °C, air humidity 20% - 80% |

HOUSING

| | |
|---------------------|------------------------|
| Swivel Bearing | Precision ball bearing |
| Housing Color | Grey white (RAL9002) |
| Offset | 40 mm |
| Swivel radius | 115 mm |
| Swivel interference | 230 mm |
| Dome diameter | 110.5 mm |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Steel, iron |
| Tread Material Mix | Polyurethane, casted |
| Bearing | Hub motor |
| Tread Color | Slate grey (RAL7015) |
| Threadguards | Integrated threadguard |
| Diameter | 150 mm |
| Tread width | 50 mm |
| Hardness of tread (A) | 85 Shore A |

FITTING

| | |
|--------------|--|
| Fitting type | Stem with cam hole for profile bars, short version |
|--------------|--|



INTEGRAL ASSIST

ED44ETW150R36-34S35 D 9002 270°

Order number 990067061



BETTER MOBILITY. BETTER LIFE.

Product Drawings

