

MAXTECH

UAR 125X38-Ø12

EAN 4031582323160
Broj porudžbine 00030960

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	kotrljajući lezaj
Boja Tocak	Plava siva (RAL7031)
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	38 mm
dimenzija rupa osovina	12 mm
dužina glavcine	44,4 mm
Širina tela	38 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Maxtech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	300 kg
Statički Nosivost	600 kg
Temperaturni opseg (Minimalno)	-25 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,316 kg

MAXTECH

UAR 125X38-Ø12

EAN 4031582323160
Broj porudžbine 00030960



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

