

# NOVATECH

ETP 100X25-Ø25

EAN 4031582331288  
Broj porudžbine 00839111



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	100 mm
Širina omotac	25 mm
dimenzija rupa osovina	25 mm
dužina glavcine	12 mm
Širina tela	25 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	210 kg
Nosivost na 6 km/h	170 kg
Statički Nosivost	420 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,48 kg

# NOVATECH

ETP 100X25-Ø25

EAN 4031582331288  
Broj porudžbine 00839111



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

