

# AGILA

2470PIO150R05-32

EAN 4031582361193



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Agila                     |
| Housing type                | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 1.8 mph    | 176.37 lb                 |
| Load capacity Static        | 352.74 lb                 |
| Temperature range (Minimum) | -4 °F                     |
| Temperature range (Maximum) | 140 °F                    |
| Overall height              | 7.4 in                    |
| Overall weight              | 2.4 lb                    |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread material        | Solid rubber, non-marking |
| Bearing               | Plain bearing             |
| Threadguards          | Without threadguard       |
| Diameter              | 5.91 in                   |
| Tread width           | 1.26 in                   |
| Hardness of tread (A) | 80 Shore A                |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material            | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Offset              | 1.77 in             |
| Swivel radius       | 4.72 in             |
| Swivel interference | 9.45 in             |

## FITTING

|               |                   |
|---------------|-------------------|
| Fitting type  | Solid stem, round |
| Bolt diameter | 1.26 in           |
| Bolt length   | 1.77 in           |

# AGILA

2470PIO150R05-32

EAN 4031582361193



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

