

PRODUCT INFORMATION

NOVATECH

ITP 125x30-Ø15 HL45

EAN 4031582319873



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.18 in
Axle hole diameter	0.59 in
Hub length	1.77 in
Body width	1.18 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ● ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	925.94 lb
Load capacity at 3.7 mph	738.55 lb
Electric conductive	no
Stainless	no
Load capacity Static	1851.88 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	1.06 lb




PRODUCT INFORMATION

NOVATECH

ITP 125x30-015 H145

EAN 4031582319873

Order number 00829478



BETTER MOBILITY. BETTER LIFE.