

AGILA

2470PJO100R07-Ø19-21,5

EAN 4031582324853



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	176.37 lb
Load capacity Static	352.74 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	5.43 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.26 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.5 in
Swivel radius	3.46 in
Swivel interference	6.93 in

FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	0.75 in
Expander fitting (Maximum)	0.85 in
Hint	Please indicate required tube innerdiameter when ordering.

AGILA

2470PJO100R07-Ø19-21,5

EAN 4031582324853



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

