PRODUCT INFORMATION

LINEA CLINIC

5946UAC150R36-32S27 safety OH155

EAN 4031582412819



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Linea clinic
Type	Swivel caster with central , total lock
Standard	similar EN12531- Hospital Bed Castors
Load capacity at 1.8 mph	330.69 lb
Load capacity at 2.5 mph	330.69 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	661.39 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	6.1 in
Overall width	2.8 in
Overall weight	2.41 lb
Certification	Tested and monitored by TÜV Süd

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Offset	1.87 in
Swivel radius	4.82 in
Swivel interference	10 in

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	5.91 in
Tread width	0.59 in
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Stem with cam hole for profile bars, short version
Bolt diameter	1.26 in
Bolt length	1.97 in
Hint	Washable beds must be sealed in the fitting area by the hospital bed manufacturer.

Deutscher Designer Club

IF Design Award

Interzum Award

© Copyright 2026 TENTE International GmbH


LINEA CLINIC


5946UAC150R36-32S27 safety OH155

EAN 4031582412819

BETTER MOBILITY. BETTER LIFE.

Product Drawings





Deutscher Designer Club

IF Design Award

Interzum Award

© Copyright 2026 TENTE International GmbH