

DURATECH

TOP 085X85-Ø20 HL85

EAN 4031582331219
Order number 00832615



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	85 mm
Tread width	85 mm
Axle hole diameter	20 mm
Hub length	85 mm
Body width	85 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	800 kg
Load capacity at 6 km/h	640 kg
Load capacity Static	1600 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.566 kg

DURATECH

TOP 085X85-Ø20 HL85

EAN 4031582331219
Order number 00832615



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

