

NOVATECH

ETP082X90-Ø20 HL90

EAN 4031582452983



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	82 mm
Tread width	90 mm
Axle hole diameter	20 mm
Hub length	90 mm
Hardness of tread (A)	92 Shore A
Bearing type	6204

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Load capacity at 3 km/h	750 kg
Load capacity Static	1500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	1.158 kg

TECHNICAL DRAWINGS

