PRODUCT INFORMATION

DURATECH SILENT

HUR 100x36-Ø12 HL44 tyre-black

EAN 4031582319637



Image may differ from the original product

WHEEL

Body material	Damping, hybrid material
Tread Material Mix	Polyamide
Bearing	Roller bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	36 mm
Axle Hole Diameter	12 mm
Hub Length	44 mm
Body width	36 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech silent
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Electric Conductive	No
Stainless	No
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.4 kg

© Copyright 2026 TENTE International GmbH


DURATECH SILENT

HUR 100x36-Ø12 HL44 tyre-black

EAN 4031582319637

Order number 00033610

Product Drawings



© Copyright 2026 TENTE International GmbH