

# DURATECH

U00050X20-Ø8 NATUR

EAN 4031582447699



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.79 in
Axle hole diameter	0.31 in
Hub length	0.85 in
Hardness of tread (D)	75 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	121.25 lb
Load capacity Static	242.51 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.04 lb

# DURATECH

U00050X20-Ø8 NATUR

EAN 4031582447699



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

