

# LINEA CLINIC

5944UAC125R36-32S30OH150 4xM6

EAN 4031582360035



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                                       |
|-----------------------------|-------------------------------------------------------|
| Product name                | Linea clinic                                          |
| Type                        | Swivel caster with central, total or directional lock |
| Standard                    | similar EN12531- Hospital Bed Castors                 |
| Load capacity at 1.8 mph    | 330.69 lb                                             |
| Load capacity at 2.5 mph    | 330.69 lb                                             |
| Electric conductive         | no                                                    |
| Stainless                   | Yes                                                   |
| Load capacity Static        | 661.39 lb                                             |
| Temperature range (Minimum) | -4 °F                                                 |
| Temperature range (Maximum) | 176 °F                                                |
| Overall height              | 5.91 in                                               |
| Overall width               | 2.8 in                                                |
| Overall weight              | 2.17 lb                                               |
| Certification               | Tested and monitored by TÜV Süd                       |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Housing Material    | Polyamide              |
| Fork shape          | Twin wheel housing     |
| Swivel bearing      | Precision ball bearing |
| Offset              | 1.57 in                |
| Swivel radius       | 4.04 in                |
| Swivel interference | 8.07 in                |

## WHEEL

|                       |                                   |
|-----------------------|-----------------------------------|
| Body material         | Polyamide                         |
| Tread material        | Polyurethane, injected            |
| Bearing               | Precision ball bearing, stainless |
| Threadguards          | With threadguard                  |
| Diameter              | 4.92 in                           |
| Tread width           | 0.59 in                           |
| Hardness of tread (A) | 92 Shore A                        |

## FITTING

|               |                                                                                    |
|---------------|------------------------------------------------------------------------------------|
| Fitting type  | Stem with cam hole for profile bars, short version                                 |
| Bolt diameter | 1.26 in                                                                            |
| Bolt length   | 1.97 in                                                                            |
| Hint          | Washable beds must be sealed in the fitting area by the hospital bed manufacturer. |

Deutscher  
Designer  
ClubInterzum  
Awardproduct  
design  
awardIF Design  
Award

# LINEA CLINIC


5944UAC125R36-32S30OH150 4xM6

EAN 4031582360035



BETTER MOBILITY. BETTER LIFE.

## Product Drawings



Deutscher  
Designer  
Club



Interzum  
Award



IF Design  
Award  
product  
design  
award