

## NOVATECH

ETY 070X20-Ø20 HL12

EAN 4031582331233  
Broj porudžbine 00835405

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

|                            |                                   |
|----------------------------|-----------------------------------|
| Materijal za telo          | Čelik, gvožđe                     |
| materijal omotaca          | Poliuretana, liveno               |
| Nošenje                    | precizini kuglicni lezaj (RS/2RS) |
| Boja Tocak                 | Med žuta (RAL1005)                |
| stitnici omotaca           | Sa threadguard                    |
| Prečnik                    | 70 mm                             |
| Širina omotac              | 20 mm                             |
| dimenzija rupa osovina     | 20 mm                             |
| duzina glavcine            | 12 mm                             |
| Širina tela                | 20 mm                             |
| Teškoća gazećeg omotac (A) | 92 Šor A                          |
| Teškoća gazećeg omotac (D) | 42 Šor D                          |

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ● ○ |
| Buka u pokretu         | ● ● ● ○ ○ |
| Ishrana                | ● ● ● ● ○ |
| otpornost na rdju      | ● ● ● ○ ○ |

## OSNOVNI ATRIBUTI

|                                |                              |
|--------------------------------|------------------------------|
| Naziv proizvoda                | Novatech                     |
| Standard                       | EN12532 - transportna oprema |
| Nosivost na 4 km/h             | 120 kg                       |
| Nosivost na 6 km/h             | 100 kg                       |
| Statički Nosivost              | 240 kg                       |
| Temperaturni opseg (Minimalno) | -10 °C                       |
| Opseg temperature (maksimalni) | 60 °C                        |
| Ukupna težina                  | 0,155 kg                     |

# NOVATECH

ETY 070X20-Ø20 HL12

EAN 4031582331233  
Broj porudžbine 00835405



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

