

# NOVATECH

ETY 070X20-Ø20 HL12

EAN 4031582331233  
Broj porudžbine 00835405

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj (RS/2RS)
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	70 mm
Širina omotac	20 mm
dimenzija rupa osovina	20 mm
dužina glavčine	12 mm
Širina tela	20 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	120 kg
Nosivost na 6 km/h	100 kg
Statički Nosivost	240 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,155 kg

# NOVATECH

ETY 070X20-Ø20 HL12

EAN 4031582331233

Broj porudžbine 00835405



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

