

COMPACTA

1430POI025P60-35X30

EAN 4031582336658
Order number 00032081



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	22.05 lb
Load capacity Static	44.09 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	1.42 in
Overall width	0.94 in
Overall weight	0.07 lb

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	0.98 in
Tread width	0.47 in
Body width	0.47 in
Hardness of tread (D)	65 Shore D

HOUSING

Material	Steel sheet, light
Fork shape	Broad
Swivel bearing	One ball race
Color	Blue passivated
Offset	0.35 in
Swivel radius	0.85 in
Swivel interference	1.69 in
Dome diameter	0.96 in

FITTING

Fitting type	Rectangular plate
Plate length	1.38 in
Plate width	1.18 in
Plate hole length (Maximum)	0.91 in
Plate hole width (Maximum)	1.1 in
Plate hole diameter	0.17 in

COMPACTA

1430POI025P60-35X30

EAN 4031582336658
Order number 00032081



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

