

MONO

A025PJI050L51-10 CHROME

EAN 4031582364606



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●●○

OSNOVNI ATRIBUTI

Naziv proizvoda	Mono
Tip	Okreni Tocak sa kocnica tocka
Standard	EN12528 - tockovi za namestaj
Nosivost na 3 km/h	30 kg
Statički Nosivost	60 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	72 mm
Ukupna težina	0,78 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	klizni lezaj sa caura cevi
štitnici omotaca	Bez stražara
Prečnik	50 mm
Širina omotac	18 mm
Teškoća gazećeg omotac (A)	85 Šora A

KUCISTE

Materijal	polipropilen
oblik viljuska	Zatvoreno
okretni lezaj	stablo , okretanje
ofset	25 mm
okretni radijus	71,8 mm
Otpor okretanju	143,6 mm

PRILAGOĐAVANJE

Tip uklapanja	zatvorena rupa za postavljanje B10
dimenzija rupa sraf	10 mm

MONO

A025PJI050L51-10 CHROME

EAN 4031582364606



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

