

ALPHA STAINLESS

8478UFX100P62

EAN 4031582339390
Order number 00035116



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	128 mm
Overall width	85 mm
Overall weight	0.595 kg

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, sealed
Axle	Screwed with nut
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	100 mm
Tread width	34 mm
Body width	34 mm
Hardness of tread (A)	63 Shore A

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Colour	Stainless steel

FITTING

Fitting type	Rectangular plate
Plate length	100 mm
Plate width	85 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	60 mm
Plate hole width (Minimum)	77 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	9 mm

ALPHA STAINLESS

8478UFX100P62

EAN 4031582339390
Order number 00035116



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

