

MAXTECH

PAP3X1.25-Ø9.8 HL41

EAN 4031582436167



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	3 in
Tread width	1.25 in
Axle hole diameter	0.39 in
Hub length	1.61 in
Hardness of tread (D)	41 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 1.8 mph	224.87 lb
Load capacity Static	449.74 lb

MAXTECH

PAP3X1.25-Ø9.8 HL41

EAN 4031582436167



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

