

ELASTECH

RK.XLR 125X40-Ø20 HL44 ESD

EAN 4031582508383
Order number 10011100



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Undefined
Tread hardness	soft
Tread material	Polypropylene, soft
Diameter	125 mm
Tread width	40 mm
Hardness of tread (A)	63 Shore A

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.387 kg

ELASTECH

RK.XLR 125X40-Ø20 HL44 ESD

EAN 4031582508383
Order number 10011100



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

WB. XLR125x40-Ø20NL44 antistatic

