

# MAXTECH

UAP160X40-Ø20 HL60 RED

EAN 4031582322989



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	160 mm
Tread width	40 mm
Axle hole diameter	20 mm
Hub length	60 mm
Hardness of tread (D)	60 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	350 kg
Load capacity at 6 km/h	300 kg
Load capacity Static	700 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.775 kg

# MAXTECH

UAP160X40-Ø20 HL60 RED

EAN 4031582322989



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

