

# PURETECH

FVP300X85-25

EAN 4031582429732



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Casting
Tread material	Solid rubber, black
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	300 mm
Tread width	85 mm
Axle hole diameter	25 mm
Hub length	92 mm
Hardness of tread (A)	67 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Housing type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	960 kg
Load capacity at 6 km/h	800 kg
Load capacity Static	1920 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	14.44 kg

# PURETECH

FVP300X85-25

EAN 4031582429732



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

