

# AGILA

2477PJP075P40

EAN 4031582050431  
Order number 00004470



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila                         |
| Housing type                | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 1.8 mph    | 165.35 lb                     |
| Load capacity Static        | 330.69 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall height              | 3.94 in                       |
| Overall width               | 1.69 in                       |
| Overall weight              | 0.75 lb                       |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Wheel color           | Silver gray (RAL7001)  |
| Threadguards          | With threadguard       |
| Diameter              | 2.95 in                |
| Tread width           | 0.98 in                |
| Body width            | 0.98 in                |
| Hardness of tread (A) | 87 Shore A             |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material            | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Color               | Blue passivated     |
| Offset              | 0.94 in             |
| Swivel radius       | 3.15 in             |
| Swivel interference | 6.3 in              |
| Dome diameter       | 1.69 in             |

## FITTING

|                             |              |
|-----------------------------|--------------|
| Fitting type                | Square plate |
| Plate length                | 2.36 in      |
| Plate width                 | 2.36 in      |
| Plate hole length (Minimum) | 1.5 in       |
| Plate hole length (Maximum) | 1.89 in      |
| Plate hole width (Minimum)  | 1.5 in       |
| Plate hole width (Maximum)  | 1.89 in      |
| Plate hole diameter         | 0.25 in      |

# AGILA

2477PJP075P40

EAN 4031582050431  
Order number 00004470



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

