PRODUCT INFORMATION

# STORA

2370PIP125S74

EAN 4031582369328

BETTER MOBILITY. BETTER LIFE.

Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●○○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product name | Stora |
| Type | Swivel caster |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 220.46 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 6.06 in |

## HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Slim |
| Swivel bearing | Two ball races |
| Offset | 1.5 in |
| Swivel radius | 3.96 in |
| Swivel interference | 7.91 in |

## WHEEL

| | |
|---|---|
| Tread hardness | soft |
| Body material | Polypropylene |
| Tread material | Solid rubber, non-marking |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 4.92 in |
| Tread width | 1.26 in |
| Hardness of tread (A) | 75 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Threaded stem with hexagon neck, top, riveted |

© Copyright 2026 TENTE International GmbH