

ALPHA STAINLESS

8477UAD100P30-11 RED

EAN 4031582370164



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●●●

OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha stainless
Tip	Okreni Tocak sa potpuna kocnica
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	150 kg
nerdjajuci	✓
Statički Nosivost	300 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Sveukupna visina	128 mm
Ukupna težina	0,957 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	kotrljajuci lezaj, nerdjajuci
osovina	Završena sa navrtkom
Prečnik	100 mm
Širina omotac	32 mm
Teškoća gazećeg omotac (D)	42 Šor D

KUCISTE

Materijal	nerdjajuci čelik, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	41 mm
Otpor okretanju	242 mm

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	11 mm

ALPHA STAINLESS

8477UAD100P30-11 RED

EAN 4031582370164



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

