

# ALPHA

3480PQR260P65 BLACK/DARKBLUE

EAN 4031582438239



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor
Load capacity at 1.8 mph	330.69 lb
Load capacity Static	661.39 lb
Overall height	12.2 in
Overall weight	11.02 lb

## WHEEL

Body material	Polypropylene
Tread material	Pneumatic tire, block profile
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	10.24 in
Tread width	3.35 in

## HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races, reinforced or stainless
Offset	3.54 in
Swivel radius	8.66 in
Swivel interference	17.32 in

## FITTING

Fitting type	Rectangular plate
Plate length	7.87 in
Plate width	6.3 in
Plate hole length (Maximum)	6.3 in
Plate hole width (Maximum)	4.72 in
Plate hole diameter	0.55 in

PRODUCT INFORMATION

# ALPHA

3480PQR260P65 BLACK/DARKBLUE

EAN 4031582438239



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

