

# STYLEA

## 5925UOI065L51-10 KICK PEDAL

EAN 4031582404067



Image may differ from the original product

### PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion Resistance	● ● ● ● ○ ○

### CORE ATTRIBUTES

Product Name	Stylea
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Electric Conductive	No
Stainless	No
Load capacity Static	100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	68 mm
Overall width	46 mm
Overall weight	0.1 kg



BETTER MOBILITY. BETTER LIFE.

### HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Stem, swiveling
Swivel radius	67 mm
Swivel interference	134 mm
Dome diameter	23 mm

### WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	65 mm
Tread width	13.9 mm

### FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

# STYLEA

5925UOI065L51-10 KICK PEDAL

EAN 4031582404067



BETTER MOBILITY. BETTER LIFE.

Product Drawings

