

# AGILA

2470PJP100R47-21,5-24

EAN 4031582325300



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

### CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Agila                     |
| Housing type                | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 1.8 mph    | 220.46 lb                 |
| Load capacity Static        | 440.92 lb                 |
| Temperature range (Minimum) | 14 °F                     |
| Temperature range (Maximum) | 104 °F                    |
| Overall height              | 5.43 in                   |
| Overall weight              | 1.54 lb                   |

### WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 3.94 in                |
| Tread width           | 1.26 in                |
| Hardness of tread (A) | 87 Shore A             |

### HOUSING

|                     |                     |
|---------------------|---------------------|
| Material            | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Offset              | 1.5 in              |
| Swivel radius       | 3.46 in             |
| Swivel interference | 6.93 in             |

### FITTING

|                            |                                                            |
|----------------------------|------------------------------------------------------------|
| Fitting type               | Synthetic expander, square                                 |
| Expander fitting (Minimum) | 0.85 in                                                    |
| Expander fitting (Maximum) | 0.94 in                                                    |
| Hint                       | Please indicate required tube innerdiameter when ordering. |

# AGILA

2470PJP100R47-21,5-24

EAN 4031582325300



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

