

NOVATECH

ETY 060x25-Ø20 HL12

EAN 4031582318470



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing (RS/2RS)
Wheel Color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	60 mm
Tread width	25 mm
Axle Hole Diameter	20 mm
Hub Length	12 mm
Body width	25 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	140 kg
Load capacity at 6 km/h	110 kg
Electric Conductive	No
Stainless	No
Load capacity Static	280 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.16 kg

