

PRODUCT INFORMATION

NOVATECH

FTP200x75-Ø25 HL75

EAN 4031582428827



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES


Product name	Novatech
Type	Wheel
Electric conductive	no
Stainless	no
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	17.61 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	7.87 in
Tread width	2.95 in
Axle hole diameter	0.98 in
Hub length	2.95 in
Hardness of tread (A)	92 Shore A




PRODUCT INFORMATION

NOVATECH

FTP200x75-Ø25 H175

EAN 4031582488577



BETTER MOBILITY. BETTER LIFE.