

PRODUCT INFORMATION

NOVATECH

FTP200x75-Ø25 HL75

EAN 4031582428827



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES


|                             |          |
|-----------------------------|----------|
| Product name                | Novatech |
| Type                        | Wheel    |
| Electric conductive         | no       |
| Stainless                   | no       |
| Temperature range (Minimum) | -4 °F    |
| Temperature range (Maximum) | 140 °F   |
| Overall weight              | 17.61 lb |



BETTER MOBILITY. BETTER LIFE.

WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Casting                |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 7.87 in                |
| Tread width           | 2.95 in                |
| Axle hole diameter    | 0.98 in                |
| Hub length            | 2.95 in                |
| Hardness of tread (A) | 92 Shore A             |




PRODUCT INFORMATION

**NOVATECH**

FTP200x75-Ø25 H175

EAN 4031582488577



BETTER MOBILITY. BETTER LIFE.