PRODUCT INFORMATION

DURATECH

UOD125x43-Ø20 LM58 TFR

EAN 4031582485332

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Roller bearing, stainless
Diameter	125 mm
Tread width	43 mm
Axle Hole Diameter	20 mm
Hub Length	58 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●●
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	350 kg
Electric Conductive	No
Stainless	No
Load capacity Static	700 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.57 kg

© Copyright 2026 TENTE International GmbH


DURATECH

UOD125x43-Ø20 LM58 TFR

EAN 4031582485332

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH