

# LINEA

5947UAP125R05-22 RAL9002

EAN 4031582369168



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ●   |
| Movement Noise       | ● ● ● ○ ○   |
| Attrition            | ● ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Linea                         |
| Type                        | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 130 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 260 kg                        |
| Temperature range (Minimum) | -10 °C                        |
| Temperature range (Maximum) | 40 °C                         |
| Overall Height              | 145 mm                        |
| Overall width               | 82 mm                         |
| Overall weight              | 1.07 kg                       |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Housing Material    | Polyamide              |
| Fork shape          | Twin wheel housing     |
| Swivel Bearing      | Precision ball bearing |
| Housing Color       | Grey white (RAL9002)   |
| Offset              | 40 mm                  |
| Swivel radius       | 129 mm                 |
| Swivel interference | 258 mm                 |
| Dome diameter       | 52 mm                  |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polyamide              |
| Tread Material Mix    | Polyurethane, injected |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 125 mm                 |
| Tread width           | 20 mm                  |
| Hardness of tread (A) | 92 Shore A             |

## FITTING

|               |                   |
|---------------|-------------------|
| Fitting type  | Solid stem, round |
| Bolt diameter | 22 mm             |
| Bolt length   | 40 mm             |



Deutscher  
Designer  
Club



Interzum  
Award



product  
design  
award

IF Design  
Award

# LINEA

5947UAP125R05-22 RAL9002

EAN 4031582369168



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

---

