

ALPHA STAINLESS

8478POO100P62-WHITE TFR

EAN 4031582480535



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------|
| Product name | Alpha stainless |
| Housing type | Fixed castor |
| Load capacity at 3 km/h | 150 kg |
| Load capacity Static | 300 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 128 mm |
| Overall weight | 0.445 kg |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing |
| Axle | Screwed with nut |
| Threadguards | Without threadguard |
| Diameter | 100 mm |
| Tread width | 36 mm |
| Hardness of tread (A) | 98 Shore A |

HOUSING

| | |
|---------------|------------------------|
| Material fork | Stainless steel, heavy |
| Fork shape | Broad |
| Stainless | ✓ |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 100 mm |
| Plate width | 85 mm |
| Plate hole length (Minimum) | 77 mm |
| Plate hole length (Maximum) | 80 mm |
| Plate hole width (Maximum) | 60 mm |
| Plate hole diameter | 9 mm |

ALPHA STAINLESS

8478POO100P62-WHITE TFR

EAN 4031582480535



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

