

SUPRATECH

PJR 125X32-Ø12 HL44,4

EAN 4031582320541
Order number 00030820



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Roller bearing
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	32 mm
Axle hole diameter	12 mm
Hub length	44.4 mm
Body width	32 mm
Hardness of tread (A)	87 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.214 kg

SUPRATECH

PJR 125X32-Ø12 HL44,4

EAN 4031582320541
Order number 00030820



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

