

PURETECH

PVR 300X50-Ø20 HL58

EAN 4031582321357
Broj porudžbine 00038262

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	250 kg
Statički Nosivost	500 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	2,821 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
Boja Tocak	Grafitna crna (RAL9011)
stitnici omotaca	Bez stražara
Prečnik	300 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavcine	58 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PURETECH

PVR 300X50-Ø20 HL58

EAN 4031582321357
Broj porudžbine 00038262



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

