

PURETECH AIR

PPO400X100-Ø20 HL74 4PR TFR

EAN 4031582394078



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Pneumatic tyre, line profile
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	400 mm
Tread width	100 mm
Axle hole diameter	20 mm
Hub length	74 mm
Hardness of tread (A)	55 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech air
Housing type	Wheel
Load capacity at 3 km/h	140 kg
Load capacity Static	280 kg
Overall weight	1.89 kg

PURETECH AIR

PPO400X100-Ø20 HL74 4PR TFR

EAN 4031582394078



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

