

## ALPHA

3478UOH160P63

EAN 4031582307047  
Order number 00000804



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha                         |
| Type                        | Fixed castor                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 350 kg                        |
| Load capacity Static        | 700 kg                        |
| Temperature range (Minimum) | -40 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall height              | 200 mm                        |
| Overall width               | 115 mm                        |
| Overall weight              | 1.568 kg                      |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide                 |
| Tread material        | Identical with wheel body |
| Bearing               | Plain bearing             |
| Axle                  | Screwed with nut          |
| Wheel color           | Natural white             |
| Threadguards          | With threadguard          |
| Diameter              | 160 mm                    |
| Tread width           | 40 mm                     |
| Body width            | 40 mm                     |
| Hardness of tread (D) | 75 Shore D                |

## HOUSING

|               |                    |
|---------------|--------------------|
| Material fork | Steel sheet, heavy |
| Fork shape    | Broad              |
| Colour        | Blue passivated    |

## FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Medium rectangular plate |
| Plate length                | 137 mm                   |
| Plate width                 | 115 mm                   |
| Plate hole length (Minimum) | 75 mm                    |
| Plate hole length (Maximum) | 80 mm                    |
| Plate hole width (Minimum)  | 75 mm                    |
| Plate hole width (Maximum)  | 105 mm                   |
| Plate hole diameter         | 11 mm                    |

# ALPHA

3478UOH160P63

EAN 4031582307047  
Order number 00000804



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

