

# NOVATECH

ETP060X20-Ø20 HL12

EAN 4031582419030



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Steel, iron            |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 60 mm                  |
| Tread width           | 20 mm                  |
| Axle hole diameter    | 20 mm                  |
| Hub length            | 12 mm                  |
| Hardness of tread (A) | 92 Shore A             |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |          |
|-----------------------------|----------|
| Product name                | Novatech |
| Housing type                | Wheel    |
| Load capacity at 3 km/h     | 100 kg   |
| Load capacity Static        | 200 kg   |
| Temperature range (Minimum) | -20 °C   |
| Temperature range (Maximum) | 60 °C    |
| Overall weight              | 0.14 kg  |

## TECHNICAL DRAWINGS

