

# ALPHA STAINLESS

8478PJD200P63 TFR

EAN 4031582386813



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha stainless               |
| Housing type                | Fixed castor                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 200 kg                        |
| Load capacity Static        | 400 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall height              | 240 mm                        |
| Overall weight              | 1.813 kg                      |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread material        | Thermoplastic rubber      |
| Bearing               | Roller bearing, stainless |
| Axle                  | Screwed with nut          |
| Diameter              | 200 mm                    |
| Tread width           | 46 mm                     |
| Hardness of tread (A) | 87 Shore A                |

## HOUSING

|               |                        |
|---------------|------------------------|
| Material fork | Stainless steel, heavy |
| Fork shape    | Broad                  |
| Stainless     | ✓                      |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 137 mm            |
| Plate width                 | 115 mm            |
| Plate hole length (Maximum) | 105 mm            |
| Plate hole width (Minimum)  | 75 mm             |
| Plate hole width (Maximum)  | 80 mm             |
| Plate hole diameter         | 11 mm             |