

# AGILA

2478PJP150P50

EAN 4031582030631  
Order number 00006887



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Agila                     |
| Type                        | Fixed castor              |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 1.8 mph    | 220.46 lb                 |
| Load capacity Static        | 440.92 lb                 |
| Temperature range (Minimum) | -4 °F                     |
| Temperature range (Maximum) | 140 °F                    |
| Overall height              | 7.28 in                   |
| Overall width               | 2.36 in                   |
| Overall weight              | 1.66 lb                   |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Wheel color           | Silver gray (RAL7001)  |
| Threadguards          | With threadguard       |
| Diameter              | 5.91 in                |
| Tread width           | 1.26 in                |
| Body width            | 1.26 in                |
| Hardness of tread (A) | 87 Shore A             |

## HOUSING

|               |                     |
|---------------|---------------------|
| Material      | Steel sheet, medium |
| Fork shape    | Broad               |
| Color         | Blue passivated     |
| Dome diameter | 2.36 in             |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 3.03 in           |
| Plate width                 | 2.64 in           |
| Plate hole length (Minimum) | 1.83 in           |
| Plate hole length (Maximum) | 2.03 in           |
| Plate hole width (Minimum)  | 2.2 in            |
| Plate hole width (Maximum)  | 2.42 in           |
| Plate hole diameter         | 0.33 in           |

# AGILA

2478PJP150P50

EAN 4031582030631  
Order number 00006887



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

