

LUMINA

A520PJ1050L51-8 CHROME/9011/7042

EAN 4031582357653
Order number 00074400



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	56 mm
Overall width	54 mm
Overall weight	0.065 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Traffic grey A (RAL7042)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	10 mm
Body width	10 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Offset	20 mm
Swivel radius	52 mm
Swivel interference	104 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	8 mm

PRODUCT INFORMATION

LUMINA

A520PJ1050L51-8 CHROME/9011/7042

EAN 4031582357653
Order number 00074400



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

