

PRODUCT INFORMATION

MAXTECH

UAR125x40-Ø20 HL58 BURDEOS

EAN 4031582416565



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	125 mm
Tread width	40 mm
Axle Hole Diameter	20 mm
Hub Length	58 mm
Hardness of tread (D)	40 Shore D

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Electric Conductive	No
Stainless	No
Load capacity Static	600 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.51 kg

MAXTECH

UAR125x40-Ø20 HL58 BURDEOS

EAN 4031582416565



BETTER MOBILITY. BETTER LIFE.

Product Drawings

