

# MAXTECH

PNP 175X30-Ø8 HL44

EAN 4031582320602  
Order number 00005566



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
	soft
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Wheel color	Black
Threadguards	With threadguard
Diameter	6.89 in
Tread width	1.18 in
Axle hole diameter	0.31 in
Hub length	1.73 in
Body width	1.18 in
Hardness of tread (A)	70 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	165.35 lb
Load capacity Static	330.69 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.66 lb

PRODUCT INFORMATION

# MAXTECH

PNP 175X30-Ø8 HL44

EAN 4031582320602  
Order number 00005566



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

