

ALPHA CENTRAL

3476PXU200P69 L0-11

EAN 4031582304992



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--|
| Product name | Alpha central |
| Housing type | Swivel castor with central, total lock |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 205 kg |
| Load capacity Static | 410 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 240 mm |
| Overall weight | 2.709 kg |

WHEEL

| | |
|-----------------------|---|
| Body material | Polypropylene |
| Tread material | Polyurethane, biosourced, injected, electric-conductive |
| Bearing | Plain bearing with synthetic spacer Tube |
| Axle | Screwed with nut |
| Diameter | 200 mm |
| Tread width | 50 mm |
| Hardness of tread (A) | 85 Shore A |

HOUSING

| | |
|---------------------|--------------------|
| Material fork | Steel sheet, heavy |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 55 mm |
| Swivel radius | 155 mm |
| Swivel interference | 310 mm |

FITTING

| | |
|-----------------------------|---|
| Fitting type | Rectangular plate with central locking function |
| Plate length | 137 mm |
| Plate width | 105 mm |
| Plate hole length (Maximum) | 105 mm |
| Plate hole width (Minimum) | 75 mm |
| Plate hole width (Maximum) | 80 mm |
| Plate hole diameter | 11 mm |

ALPHA CENTRAL

3476PXU200P69 L0-11

EAN 4031582304992



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

