

# STYLEA

5920UJI075L51-11D20 HH 9006/9011

EAN 4031582335996



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product name                | Stylea                      |
| Type                        | Swivel caster               |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph    | 110.23 lb                   |
| Electric conductive         | no                          |
| Stainless                   | no                          |
| Load capacity Static        | 220.46 lb                   |
| Temperature range (Minimum) | -4 °F                       |
| Temperature range (Maximum) | 140 °F                      |
| Overall height              | 3.5 in                      |
| Overall width               | 2.13 in                     |
| Overall weight              | 0.33 lb                     |

## HOUSING

|                     |                                  |
|---------------------|----------------------------------|
| Housing Material    | Polyamide                        |
| Fork shape          | Twin wheel housing               |
| Swivel bearing      | Stem, swiveling                  |
| Housing Color       | White aluminum (similar RAL9006) |
| Offset              | 1.5 in                           |
| Swivel radius       | 2.44 in                          |
| Swivel interference | 4.88 in                          |
| Dome diameter       | 0.79 in                          |

## WHEEL

|                       |                                  |
|-----------------------|----------------------------------|
| Body material         | Polyamide                        |
| Tread material        | Thermoplastic rubber             |
| Bearing               | Plain bearing with spacer tube   |
| Axle                  | Riveted                          |
| Tread color           | Graphite black (RAL9011)         |
| Wheel color           | White aluminum (similar RAL9006) |
| Threadguards          | Without threadguard              |
| Diameter              | 2.95 in                          |
| Tread width           | 0.31 in                          |
| Axle hole diameter    | 0 in                             |
| Hub length            | 0 in                             |
| Body width            | 0.31 in                          |
| Hardness of tread (A) | 87 Shore A                       |

## FITTING

|                    |                            |
|--------------------|----------------------------|
| Fitting type       | Blind hole for B10 fitting |
| Bolt hole diameter | 0.43 in                    |

# STYLEA

5920UJI075L51-11D20 HH 9006/9011

EAN 4031582335996



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

---

